



life.augmented

CPAP and medical artificial ventilators

Disclaimer for critical applications

- Product(s) indicated in this presentation are sold under ST terms and conditions and they are not designed, intended or authorized for use as a critical component in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body.
- Contact ST Sales Offices for any further details.

CPAP and medical artificial ventilators



Continuous Positive Airway Pressure (CPAP) helps patients breathe by holding open the alveoli and preventing them from completely collapsing during expiration phases.

The most important aspect in a CPAP system is the air flow control that needs to be adjusted to compensate for altitude, mask movements, and leaks as well as features including heated, humidified, airway respiratory support.

Normally, CPAP is suitable for use in institutional, home, and portable settings. It is not intended for use in Emergency Medical Service (EMS) such as an emergency transport.



Medical artificial ventilators are machines supporting patient breath by providing mechanical ventilation by pushing air into and out of the lungs, to supply breaths to a patient who is tangibly unable to breathe or breathing insufficiently.

Modern ventilators are computerized controlled machines, mainly used in Intensive Care Unit (ICU), in Emergency Medical Service (as standalone units) and in Anesthesiology (as a component of an anesthesia machine).

Block diagram - Ventilators


Enhance application safety

Sense the injected air flow

Drive pumps and valves

Commands & display

Perform precise motor control algorithms



Patient monitoring in ICU

Patient monitoring equipment provides medical staff with the means to continuously observe a patient's vital signs, such as the heart's electrical activity (with an electrocardiogram), over an extended period.


They come in a variety of designs including bed-side monitors for hospital use and portable devices for home use.

In Intensive Care Unit (ICU) they become life sustain devices including a series of on-fly checks which alerts the medical staff in case of anomalies in the patient vital signs.



Block diagram – Patient monitoring

Read and monitor



Protect patient

Show patient vital signs

Connect and alert medical staff

ST offer in healthcare CPAP and medical artificial ventilators




ST product offering for healthcare

ST is a trusted provider of high-quality technical solutions enabling the development of breakthrough medical systems



Acquiring data

- Sensors for Imaging
- MEMS* & measurement ICs
- Electronic interfacing



Processing data

- Powerful microcontrollers
- Artificial Intelligence at the edge
- Specially developed devices



Motion Control

- Precise and reliable motor driver
- Leadership in High Voltage MOSFET
- Wide bandgap transistors (SiC & GaN)



Security

- Secure element for medical data integrity
- M2M-SIM for authentication and confidentiality
- Enabling Blockchain transactions



Connectivity


- Short-range low-power BLE, NFC
- Long range IoT (Sigfox, LoRa)
- Cellular broadband, narrowband

Targeting a broad range of applications

- Medical Imaging
- Focused Ultrasound
- Energy Harvesting and Neurostimulators
- Non-Destructive testing
- Electrocardiography (ECG)
- Photoplethysmography (PPG)
- Galvanic Skin Resistance (GSR)
- Bio Impedance functionalities
- Oxygen saturation
- Respiratory Rate
- Skin Temperature

Ventilator detailed block diagram

Part 1 – Sensor stages and motor control



Sensors to boost the performance and increase the comfort



Motion sensors

Accelerometer [IIS2DLPC]
6X IMU [ISM330DLC]

- Ultra compact size, Low power, digital, cost effective
- Enable the monitoring of posture and movements of the mask and patient head and optimize the airflow
- Guaranteed for 10 years availability



Pressure sensors

Barometric sensor [LPS22HH]
Water resistant
[LPS27HHW, LPS33HW]

- Ultra compact size, high robustness and reliability, Low power, digital, cost effective
- Enable monitoring the breathing to optimize the airflow



Microphones

Digital MEMS microphone
[IMP34DT05]

- High performance, digital
- Enable voice command and, together with pressure sensor, allow the monitoring of the breathing to optimize the airflow
- Guaranteed for 10 years availability



Temperature & humidity sensors

Temperature [STTS2H]
Temperature + humidity
[HTS221]

- High accuracy, Ultra compact size, digital
- Monitoring environmental conditions (temperature & humidity) enable to optimize the airflow and improve the comfort of the patient



Imaging sensors

Time of Flight Sensors to monitor water level in the tank and Mask positioning



Time of Flight

Proximity [VL6180]

Distance Sensors [VL53L0X]
[VL53L1X]

- Measure Water Level
- Monitor Mask Distance from face
- People counting or Presence detection




Complementary uses of Imaging Sensors

Ambient Light and Color sensors

Tiny color sensors for Lux/CCT and Flicker capture

Advanced Imager for computer vision

Global Shutter, High Sensitivity Vis and nIR, HDR, flicker free



Applications

- Proximity, ranging and Presence detection
- Gesture control
- Computer vision (BareCode scanning...)
- Screen brightness control for patient comfort





Current Sensing and Signal Conditioning

...



Low / High side current sense amplifier [TSC1xx, TSC2xx]

- wide range of common mode voltages from -0.3 to +26 V
- Offset voltage: $\pm 35 \mu\text{V}$ max
- Gain drift: 20 ppm/ $^{\circ}\text{C}$ max



Operation Amplifiers [TSV9xx, TSV6xx, TSZ1xx]


- Low-side current measurement for motor control
- Very-high-accuracy, (5 μV) zero-drift, micropower 5 V op amp





STM32 for healthcare application

A broad offering



Arm® Cortex® core

-M0

-M0+

-M3

-M33

-M4

-M7

dual -A7& -M4




life.augmented

● Cortex-M0+ Radio co-processor




STM32G4 series

Ideal for applications requiring an MCU that offers advanced and rich analog peripherals


Performance

- 213 DMIPS and 550 CoreMark® results
- Better dynamic power consumption (163 μ A/MHz)
- Mathematical accelerators



Rich Integrated Analog and Digital

- Op-Amps (Built-in gain), DACs, Comparators
- 12-bit ADCs 4Msps with hardware oversampling
- High resolution timer (184 ps)
- USB type-C Power Delivery 3.0



Safety and security focus

- Dual Bank Flash with ECC (error code correction)
- Securable Memory Area
- Hardware encryption AES-256
- SIL, Class-B
- SRAM with Parity bit

KEY BENEFITS FOR VENTILATORS

- Easy interfacing with motor drivers and sensor stages
- Low power consumption to address portable devices
- Built-in security features

Secure Live Upgrade

Functional safety design packages



STM32L5 series

Ideal for applications requiring an MCU that offers advanced and rich analog peripherals




Security focus
Protection from hackers

Electronic Medical Records

Very power consumption
Long lifetime, small battery size

Integration, size & performance
Best fit to application requirements

Security: TrustZone for isolation






STM32H7 series

The best choice for controls, indicators, and interfaces of ventilators



New performance record

2424 + 800 CoreMark (Cortex®-M7 @480Mhz + Cortex®-M4 @240Mhz)



Display nice graphics

The Chrom-ART Accelerator and MJPEG coded, offload the CPU by more than 90%



Advanced security features

Crypto Hash, Cortex®-M7 Security services



Rich eco-system to speed-up your design

SW tools, HW boards, community and partners






Motor control

Leading integration, performance, efficiency



Monolithic Low Voltage
STSPIN2 Series



Monolithic
STSPIN8 Series




Monolithic
L647 Series,
L620, L622 Series



System-in-Package
PowerSTEP Series

Controllers: STSPIN32 Series, L648 Series



Applications up to 10 W

Applications up to 70 W

Applications up to 500 W

- **Wide V & I ranges supported**

- 1.8 V – 85 V
- 0.6 A_{RMS} – 3 A_{RMS}


- **Intelligent top class 3phase BLDC drivers**

- **State of the art products and features for Stepper motors**



STSPIN800 series motor drivers

Compact, energy conscious and cost-competitive motor drivers



Product	Description	V _{IN} min (V)	V _{IN} max (V)	R _{DS(on)} HS+LS (Ohm)	I _{OUT} max (Arms)
STSPIN820	Microstepping driver up to 256 microsteps	7	45	1	1.5
STSPIN830	3-phase 3shunts BLDC motor driver				
STSPIN840	Dual brushed DC motor driver	7	45	1 (0.5 *)	1.5 (3 *)

(*) Features allowed in parallel mode driving

KEY BENEFITS FOR VENTILATORS

High efficiency

- Standby mode to minimize power consumption in idle state (<50µA)

Smooth and silent motion

- Smooth and silent motion thanks to I control and 256 µsteps
- FOC & 6-step FW support

Reliable thanks to full set of protections

- UVLO, non-dissipative over-current and thermal protection



Stepper motor solutions: L647x & L648x

Highly autonomous solutions using high-level motion commands from system host

Topology	Product	Description	V _{IN} min (V)	V _{IN} max (V)	R _{DSON} (Ohm)	I _{OUT} max (Arms)
Motor Drivers	L6470	Voltage mode driving algorithm (1/128 μstep)	8	45	0.3	3
	L6472	Predictive current control Adaptive decay (1/16 μstep)				
	L6474	Adaptive decay(1/16 μstep)				
Controllers	L6480	Voltage mode driving algorithm (1/128 μstep)	7.5	85	not applicable	
	L6482	Predictive current control Adaptive decay (1/16 μstep)				

KEY BENEFITS FOR VENTILATORS

System stability and low noise

- System stability and low noise:
- Adaptive auto regulated decay (slow /fast /mixed decay) (*)

Accurate positioning and control

- Predictive current control (*)

Smooth & very silent motion

- Voltage mode control (*) ensure driving performance similar to BLDC ones


Power Scalability

- Using L648x controller with ST power MOSFET (F7 family)
- (*) ST patented features



Motion Control Architecture

Best Fit for BLDC: combining Power Density and Intelligence



Architecture	Benefits
1 STSPIN32 MCU + Driver	<ul style="list-style-type: none"> • High integration (MCU + 3 Ph. Driver + DC-DC + LDO + Protection) • High performance control • High speed sensorless FOC
2 STSPIN L6230 Driver + MOS	<ul style="list-style-type: none"> • Integrated Power Stage & Protections • Good cost-performance trade-off
3 STDRIVE Discrete	<ul style="list-style-type: none"> • Best flexible partitioning • Good cost-performance trade-off

KEY BENEFITS FOR VENTILATORS

Address all architectures of CPAP and Respirators

Cost effective sensor-less systems or accurate control with Hall-effect sensor feedback




MDmesh™ family: Super-junction power MOSFET

Leader in High Voltage Silicon MOSFET




Defibrillator Medical machine X-Ray machine Ventilator



Medical AC-DC SMPS



or



Complete family with wide product portfolio in terms of $R_{DS(on)}$, BV_{dss} and packaging to reach the right mix for high efficiency and compactness solution

MDmesh™ series:

- M2, M5 on PFC section
- M2, DM2, on DC/DC section
- NM, K5 on flyback

Main Products

- STF18N60M2
- STF40N60M2
- STY112N65M5
- STY145N65M5
- STP11NM80
- STD3N80K5
- STW40N95K5



Customers:

Delta, Edan, Megmeet, Plexus, Hechuan, Mindray, Medtronic, Philips, GE



High voltage silicon MOSFET series Super-junction MDmesh™

Breakdown Voltage

600V

650V

800V – 1700V

MDmesh series

M2

M6

DM2

DM6

M5

DM2

DM6

K5

Focus Topology

Flyback,
PFC/LLC
resonant conv.

Flyback,
PFC/LLC
high efficiency

HB / FB,
ZVS, LLC

HB / FB,
ZVS, LLC
high efficiency

Hi-end-power PFC
and hard switching
topologies

HB / FB,
ZVS, LLC
high power level

HB / FB,
ZVS, LLC
high power level
high efficiency

Flyback topology

Focus Applications

Charger
adapters Led
lighting,
Medical

Server, 5G,
Consumer,
Adapters,
Solar, Medical


Solar, Server, Telecom SMPS, EV-Car/Charging, Medical

LED driver, LED
lighting, auxiliary
SMPS, EV-Car,
Medical



Ventilator detailed block diagram

Part 2 – Connectivity, security and User Interface





Secure Element: STSAFE-A

Secure element for brand protection and secure connections

Secure the connected devices

- Authentication
- Secure connection
- Secure data storage
- Signature verification
- Common criteria certified

Protect your brand (consumables / peripherals)

- Digital Motion Engine
- High-level motion commands

STSAFE-A110

Enriched secure connection & LPWAN

- Generic pre-personalized samples
- STM32 Nucleo Expansion board
- STM32Cube Software package




STM32 Open Development Environment

Available @ distribution



life.augmented





M2M-eSIM: ST4SIM solution

A wide range of cellular connectivity solutions



Connection Health
Patient care from home

ST4SIM

- Wide range SIM/eSIM solutions based on Basic, Cryptographic and GSMA SGP.02 configurations
- GSMA eSIM certified and interoperable with MNOs & Subscription Management platform
- Complete ecosystem with trusted partners for connectivity & Subscription Management Platform
- Industrial & automotive grade solutions (T° & reliability)
- Multiple packages format (4FF, MFF2, WLCSP, TSSOP20)



NFC main use cases & benefits

NFC Tag usage in medical

Configuration & Data logging


NFC



- Product configuration and parameter settings through NFC
- Data log transferred, processed and plotted on NFC phone

Servicing & Maintenance

NFC



- Contactless access to maintenance records
- Update parameters even if device is powered off thanks to NFC phone
- Quick firmware upgrade via fast transfer mode

Enhanced user experience

NFC




- Wireless pairing
- Access to web page (URL) or get link for Android (AAR) or iOS application
- E-warranty card & customer registration
- Device control with mobile phone
- User identification & personalized settings




- Interactive and zero power technology (Tag powered by Reader)
- Convenient product configuration and maintenance
- Simple and flexible





Typical NFC tag block diagrams and use in medical



ST25TV02K / ST25TA02KB

 **TruST25 digital signature**
Passwords
Easy & fast data transfer


Enhanced user experience 




ST25DV04K / 16K / 64K

 **I²C fast interface**
Fast Transfer Mode
Large memory storage

Configuration & data logging
Servicing & Maintenance
Enhanced user experience 



ST25R3911B / 12 / 13

 **High output power**
Low power consumption
Automatic antenna tuning

Configuration & data logging
Servicing & Maintenance 



UHF main use cases & benefits

Real-time patient tracking

UHF




- Log & monitor the progress of a person
- Locate people in real time
- Speed up bed turnover to admit more patients efficiently

Asset management

UHF



- Locate medical equipment
- Update parameters
- Speed up inventory management



ST25RU3993



- Long read range
- Low power consumption
- Fast read speeds




- Fast detection and long read range
- Possibility of identifying more than 200 tags without constraint of positioning
- Cheapest tag to manufacture

Real-time patient tracking
Drug asset management



ST low-power RF product lines connectivity, efficiency and robustness

Enabling the Sensor-to-Cloud wireless connectivity




- Simplified HMI
- Easy customization
- Remote reading
- Service and maintenance
- Firmware upgrade
- Added-value services



QFN48
6 x 6 mm



QFN32
5 x 5 mm



WLCSP34
2.66 x 2.56 mm

Scalable packages



S2-LP family overview

SPIRIT Family



Sub-1GHz Radio Transceivers
and LPWAN networking



Companion Balun and Filter
BALF-SPI2-01D3
BALF-SPI2-02D3

Performance

Sub
1GHz

S2-LP / S2-LPCB / S2-LPTX

- 413-479 MHz / 826-958 MHz
- 452-527 MHz / 904-1055 MHz (**)
- -40°C to +105°C
- QFN24 4x4x1



Radio performance

- 100 bps to 500 kbps
- -130 dBm @ 0.3kbps (*)
- +16 dBm output power



Ultra low-power consumption

- Sleep / Shutdown: 700nA / 2.5nA
- Rx peak: 7 mA (*)
- Tx peak: 10 mA @+10dBm

Protocols



(*) RX Feature only available on transceivers: S2-LP and S2-LPCB


(**) Frequency bands only available on S2-LPCB



Low power RF modules



BlueNRG-M0L
BlueNRG-M0A




- Based on BlueNRG-MS
- BLE4.2 certification
- Including high efficient chip antenna, filter and balun **BALF-NRG-01D3**

SPSGRF-868
SPSGRF-915



- Antenna option
- Two carrier frequency versions: 868 MHz & 915 MHz
- Including filter and balun BALF-SPI-02D3 for the SPSSGRF-868.

BlueNRG-M2SA
BlueNRG-M2SP



- Based on BlueNRG-2
- BLE5.0 certification
- Including high efficient chip antenna [-M2SA] or PCB antenna [-M2SP], filter and balun **BALF-NRG-02D3**

SPSGRFC-433
SPSGRFC-868
SPSGRFC-915




- Connector option
- Three carrier frequency versions: 433 MHz, 868 MHz and 915 MHz
- Including filter and balun BALF-SPI-01D3 for the SPSSGRFC-433.






ST protections increase EMC robustness

High system immunity for all MCU interfaces





Protections and filters in ventilators



Thank you

© STMicroelectronics - All rights reserved.

The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies. All other names are the property of their respective owners.



life.augmented